



## DEVIfoil™ Mirror

An effective system for keeping the mirror completely steam free.

Fast and easy installation where the self-adhesive side of the heating foil is placed on the back of the mirror.

Low energy consumption and automatic activation when the light is switched on.

### Benefits:

- Fast and easy installation
- Low energy consumption
- Automatic activation

### Standard compliance:

- EN Norm BS EN 60335-1:2002 + Amd. 1 to 6
- BS EN 60335-2-30:2003 + Amd. 1 & 2

### Approvals:



Type	V alue
Operation voltage	230 V~
Output	200 W/m <sup>2</sup>
Max. ambient temperature	80 °C
IP Class	IP 44
Protection class	Class II - <input type="checkbox"/>
Connection cable length	95 cm

### Types

Item no.	Type	Dimensions	Wattage	EAN no.
62000000	<b>DEVIfoil™ Mirror 17,5</b>	274 x 358 mm	17,5 W	5703466180686
62000001	<b>DEVIfoil™ Mirror 40</b>	410 x 524 mm	40,0 W	5703466180693
62000002	<b>DEVIfoil™ Mirror 70</b>	708 x 524 mm	70,0 W	5703466180709