



DEVIreg™ 530

The DEVIreg™ 530 is a simple electronic thermostat with a 2-pole switch, using a floor sensor (wire) to measure and control the desired floor temperature. It can be either flush-mounted or surface-mounted.

The thermostat has a dial for adjusting the temperature setting with a scale from ❄️ to 6.

Furthermore, the thermostat has an LED indicating the current mode (heating, standby or fault).



Benefits:

- 2-pole safety breaker
- Low standby consumption
- Sensor failure monitoring
- LED indication for fault
- Frost protection

Standard compliance:

- EN/IEC 60730-1 (general) and EN/IEC 60730-2-9 (thermostat)

Approvals:



Type	Value
Operation voltage	220 V- 240V~ 50/60 Hz
Standby power consumption	max. 0.25 W
Relay:	
Resistive load	Max 15A / 3450W @ 230V
Inductive load	Cos Φ = 0.3 max. 1A
Sensing unit	NTC 15 kOhm at 25° C
Hysteresis	± 0.4° C
Ambient temperature	-10° C. to +30° C
Frost protection	5° C - ❄️
Temperature range	5-45°C with floor sensor only
Cable specification max	1 x 4 mm ² or 2 x 2,5 mm ²
Ball pressure test temperature	75° C
Pollution degree	2 (domestic use)
Controller type	1 C
Storage temperature	-20° C to +65° C
IP class	31
Protection class	Class II - <input type="checkbox"/>
Dimensions (H/W/D)	85 mm x 85 mm x 36 mm
Weight	90 g

Types

Item no.	Product name	Type	EAN no.
140F1030	DEVIreg™ 530	With floor sensor and ELKO frame	5703466208991
140F1031	DEVIreg™ 530	With floor sensor and ELJO frame	5703466209004
140F1032	DEVIreg™ 530	With floor sensor and JUSSI frame	5703466209011
19150352	DEVIreg™ 530	10 pcs. pack with floor sensor and JUSSI frame	5703466152829
19150354	DEVIreg™ 530	10 pcs. pack with floor sensor and ELKO frame	5703466159248